



TXA664D



## KNX/DALI actuator 4 channels KNX, easy, broadcast

### Technical properties

#### Architecture

Bus system KNX

#### Functions

Multi-phase mode suitable to switch different external conductors

Function Learning function for optimised operation of compact fluorescent lamps and LED luminaires can be activated via the bus

Soft startup bulb-preserving soft startup

#### Configuration

Number of modules 6

#### Controls and indicators

Indicator lamp yes

Operation manual operation also possible without bus, e.g. on building site ; Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; Manual operation per channel via button with integrated status LED, thereby lockout of KNX function

Indication / display status LED integrated in the manual operation button

Manual selection switches / push-buttons selection switch for manual/bus operation as well as load setting

Button / push-button with illuminated programming button

#### Main electrical features

Rated current 185 mA

#### Voltage

Auxiliary voltage 230 V AC

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

#### Fuse

Fuse Cable entries slanted

#### Dimensions

Width of rail mounted device (RMD) 6 modules

#### Power

Power of the variator 3 / 1 W

#### LED control

LED

Status LED integrated in manual operation button ;  
Overload/short-circuit indicator**Connection**

Type of load	Universal and LED Retrofit
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal

**Settings**

Supported configuration modes	easy, system
Parameterisation	preset behaviour in the event of bus voltage failure/return

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Equipment**

Number of outputs	4
Type of dimmer	Dim actuator
Substation input	No
Modular expandability	No
Dimming principle	load control via DALI bus in transmission operation ; automatic load detection
low noise	very low noise

**Use**

Local operation/hand operation	Yes
--------------------------------	-----

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	Yes

**Use conditions**

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

**Identification**

Main design line	KNX
------------------	-----