



TXB201A

1 flush mounted output 4A twisted pair

Technical properties

Architecture

| | |
|-------------|----------------|
| Bus system | KNX |
| Fixing mode | flush-mounting |

Functions

| | |
|------------------|--|
| Multi-phase mode | suitable to switch different external conductors |
|------------------|--|

Configuration

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Controls and indicators

| | |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 230 V |
|------------------------------|-------|

Voltage

| | |
|----------------------------|----------------|
| Operating voltage over bus | 21...32 V DC |
| System supply voltage | 30V DC via bus |

Electric current

| | |
|--------------------------|-----|
| Number of entry circuits | 0 |
| Maximum through current | 4 A |
| Rated current | 4 A |

Power

| | |
|-------------------------------------|-------|
| Max. power with electronic transfo. | 600 W |
| Output power | 600 W |
| Max. switching power | 600 W |

Incandescent bulbs control

| | |
|------------------------------------|-------|
| Max. power with incandescent lamps | 600 W |
|------------------------------------|-------|

Connection

| | |
|-------------------|--|
| Type of contacts | 1NO |
| Bus coupling unit | with integral bus coupling unit |
| Bus connection | bus connection via connecting terminal |

Scope of delivery

| | |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

Equipment

| | |
|-------------------------------|----|
| Number of outputs | 1 |
| Bidirectional radio frequency | No |
| Modular expandability | No |

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | 0...45 °C |
| Storage/transport temperature | -20...70 °C |

Identification

| | |
|------------------|-----|
| Main design line | KNX |
|------------------|-----|