



VE106L

Enclosure,vector,IP5x,6Modules,version Austria

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	6
-------------------	---

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	113 mm
Internal depth	113 mm
Height of installed product	190 mm
Width of installed product	165 mm
Width in division units	6
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Polystyrol (PS)
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	3
--------------------------	---

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	16
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes

Standards

GWT Glow wire test	750 °C
European directive WEEE	concerned

Safety

IK protection code against mechanical impacts	IK07
REACH conform	No
Halogen free	No

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------