



VE106PN

Enclosure, vector, flush mounted, IP65, 6M, UV stable, with metric cable entry

Technical properties

Functions

With a pipe-in lead Yes

Configuration

Number of modules 6

Compatibility

Suitable for Multimedia No

Main electrical features

Nominal voltage 400 V

Voltage

Rated operational voltage in DC 1000 V DC

Electric current

Rated current 63 A

Dimensions

Depth of installed product 113 mm

Internal depth 113 mm

Height of installed product 190 mm

Width of installed product 165 mm

Width in division units 6

Thickness of sidewall material 2.5 mm

Cover, door

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Connection

Number of conduit inlets	3
--------------------------	---

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	1
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	16
--------------------------------------	----

Extension possible	No
--------------------	----

Earthing terminal block	No
-------------------------	----

Neutral terminal block	No
------------------------	----

Signal passing door	Yes
---------------------	-----

Standards

GWT Glow wire test	850 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	IK07
---	------

Protection class	isol.class II
------------------	---------------

Glow wire test	according EN 60695-2-11: 850°C
----------------	--------------------------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------