



VE106SN

Enclosure, vector, flush mounted, IP65, 6M, UV stable, without cable entry

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 6

Main electrical features

Nominal voltage 400 V

Voltage

Rated operational voltage in DC 1000 V DC

Electric current

Rated current 63 A

Dimensions

Depth of installed product 113 mm

Internal depth 113 mm

Height of installed product 190 mm

Width of installed product 165 mm

Width in division units 6

Thickness of sidewall material 2.5 mm

Cover, door

Type of door closing Latch

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment

untreated

Installation, mounting

Suitable for outdoor use

Yes

Connection

Number of conduit inlets

3

Settings

Enclosure type

Distributor empty cabinet

Equipment

Number of rows

1

Quantity of section in width

1

Quantity of rails

1

Can be accessorized

Yes

Number of openings for flange plates

16

Extension possible

No

Earthing terminal block

No

Neutral terminal block

No

Signal passing door

Yes

Standards

GWT Glow wire test

850 °C

European directive WEEE

concerned

Safety

Protection class

isol.class II

Glow wire test

according EN 60695-2-11: 850°C

Use conditions

Operating temperature

-25...40 °C