



VE110F

**Enclosure, vector, IP5x, 10M**

**Technical properties**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Functions**

With a pipe-in lead	Yes
---------------------	-----

**Configuration**

Number of modules	10
-------------------	----

**Compatibility**

Suitable for Multimedia	No
-------------------------	----

**Main electrical features**

Nominal voltage	400 V
-----------------	-------

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth of installed product	114 mm
Internal depth	114 mm
Height of installed product	210 mm
Width of installed product	237 mm
Width in division units	10
Thickness of sidewall material	2.5 mm

**Cover, door**

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Polystyrol (PS)

Type of surface treatment	untreated
<b>Installation, mounting</b>	
Suitable for outdoor use	No
<b>Connection</b>	
Number of conduit inlets	6
<b>Equipment</b>	
Number of rows	1
Quantity of section in width	1
Number of keys	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	20
Extension possible	No
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes
<b>Standards</b>	
GWT Glow wire test	750 °C
European directive WEEE	concerned
<b>Safety</b>	
IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Impact strength	IK07
<b>Use conditions</b>	
Operating temperature	-25...40 °C