



VE110PN

Enclosure,vector,flush mounted,IP65,10M,UV-stable,with metric cable entry

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	10
-------------------	----

Compatibility

Suitable for Multimedia	No
-------------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Voltage

Rated operational voltage in DC	1000 V DC
---------------------------------	-----------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	114 mm
Internal depth	114 mm
Height of installed product	210 mm
Width of installed product	237 mm
Width in division units	10
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	light grey
--------	------------

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated
Installation, mounting	
Suitable for outdoor use	Yes
Connection	
Number of conduit inlets	6
Equipment	
Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	20
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes
Standards	
GWT Glow wire test	850 °C
European directive WEEE	concerned
Safety	
Protection class	isol.class II
Glow wire test	according EN 60695-2-11: 850°C
REACH conform	No
RoHS conform	Yes
Use conditions	
Operating temperature	-25...40 °C