



TXF121

IP20

KNX interface for electrical energy meters

Technical properties

Architecture

Bus system KNX

Controls and indicators

Indication / display LC display with illumination

Main electrical features

Frequency 50/60 Hz

Voltage

Operating voltage over bus 21...32 V DC

Dimensions

Width of rail mounted device (RMD) 1 modules

Measurement

Idle power measurement YES

Connection

Bus coupling unit with integral bus coupling unit

Type of connection with screw terminals

Bus connection bus connection via connecting terminal

Type of connection direct

Settings

Supported configuration modes system

Equipment

Type of counter other

Use

Differentiation characteristic 2 - Sales with display

Differentiation characteristic 3 - Sales with integral bus coupling unit

Standards

PTB certified product 0

Safety

REACH conform No

RoHS conform Yes

Halogen free No

Use conditions

Storage/transport temperature

-25...70 °C

Identification

Main design line

KNX