



TYA604A



Output module 4x 4A /230V~, KNX

Technical properties

Architecture

Bus system yes

Functions

Multi-phase mode suitable to switch different external conductors

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

Switching For switching, e.g. of 4 independent loads or activation of 2 drives

Operating mode any combined operation from drive and switching functions possible

Configuration

Number of modules 4

Controls and indicators

Indicator lamp yes

Operation Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; manual operation per channel using button (single-area operation)

Indication / display status LED integrated in the manual operation button

Manual selection switches / push-buttons manual operation buttons for on/off (up/down) and bus function on/off per channel/device

Button / push-button with illuminated programming button

Main electrical features

Rated current 4 A

Voltage

Operating voltage over bus 21...32 V DC

Output voltage 230 V~

System supply voltage 30V DC via bus

Electric current

Bus current consumption (data transfer) 4 mA

Bus current consumption (idle) 3 mA

Number of entry circuits 0

Maximum through current 4 A

Switching current at $\cos \phi = 0.8$ max. 4 A

Dimensions

| | |
|--|--|
| Depth | 65 mm |
| Width of rail mounted device (RMD) | 4 modules |
| Height | 90 mm |
| Power | |
| Max. power with electronic transfo. | 800 W |
| Total power loss under IN | 1 W |
| Output power | 800 W |
| Conventional transformers | 800 VA |
| Electronic transformers | 800 W |
| Lighting control | |
| Fluorescent lamps with electronical ballast (EB) | 12 x 36 W |
| - uncompensated | 800 W |
| Fluorescent bulbs control | |
| Energy-saving lamps | 6 x 23 W |
| Power lighting fluo lamps | 6x23W |
| Max. power fluo. duo lamp comp. series | 12 x 36 W |
| LED control | |
| Max number of LED/CFL lamps | 6 |
| 230V LED lamps | 6 x 23 W |
| Power LED | 72 W |
| LED | Status LED integrated in manual operation button |
| Incandescent bulbs control | |
| Max. power with incandescent lamps | 800 W |
| 230 V incandescent lamps | 800 W |
| 230 V halogen lamps | 800 W |
| 230 V incandescent lamps and halogen lamps | 800 W |
| Connection | |
| Connection cross-sect. flexible conductor | 0,75 / 2,5mm ² |
| Connection cross-sect. rigid cable | 0,75 / 2.5mm ² |
| Conductor cross-section (flexible) | 0.75...2.5 mm ² |
| Conductor cross-section (rigid) | 0.75...2.5 mm ² |
| Type of contacts | 4NO |
| Bus coupling unit | with integral bus coupling unit |
| Type of connection | with QuickConnect plug-in terminals |
| Bus connection | bus connection via connecting terminal |
| Settings | |
| Supported configuration modes | system |
| Setting | switching time on change of direction adjustable |
| Scope of delivery | |
| Bus connection included | Yes |

Equipment

Modular expandability No

Use

Differentiation characteristic 3 - Sales with plug-in terminals

Safety

REACH conform No

RoHS conform Yes

Halogen free No

Use conditions

Operating temperature -5...45 °C

Storage/transport temperature -20...70 °C

Identification

Main design line KNX