



VE212F

Enclosure,vector,IP5x, 24M

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	24
-------------------	----

Compatibility

Suitable for Multimedia	No
-------------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	151 mm
Internal depth	151 mm
Height of installed product	427 mm
Width of installed product	310 mm
Width in division units	12
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	12
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	2
Quantity of section in width	1
Number of keys	1
Quantity of rails	2
Can be accessorized	Yes
Number of openings for flange plates	46
Extension possible	No
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes

Standards

GWT Glow wire test	750 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	IK08
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK08

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------