



VE218F

**Enclosure, vector, IP5x**

**Technical properties**

**Architecture**

Fixing mode surface-mounting

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 36

**Compatibility**

Suitable for Multimedia No

**Main electrical features**

Nominal voltage 400 V

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 452 mm

Width of installed product 418 mm

Width in division units 18

Thickness of sidewall material 2.5 mm

**Cover, door**

Type of door closing Latch

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

---

Type of surface treatment

untreated

---

**Installation, mounting**

---

Suitable for outdoor use

No

---

**Connection**

---

Number of conduit inlets

15

---

**Settings**

---

Enclosure type

Distributor empty cabinet

---

**Equipment**

---

Number of rows

2

---

Quantity of section in width

1

---

Number of keys

1

---

Quantity of rails

2

---

Can be accessorized

Yes

---

Number of openings for flange plates

46

---

Extension possible

No

---

Earthing terminal block

Yes

---

Neutral terminal block

No

---

Signal passing door

Yes

---

**Standards**

---

GWT Glow wire test

750 °C

---

European directive WEEE

concerned

---

**Safety**

---

Protection class

isol.class II

---

**Use conditions**

---

Operating temperature

-25...40 °C