



VE218F

Enclosure, vector, IP5x

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	36
-------------------	----

Compatibility

Suitable for Multimedia	No
-------------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	151 mm
Internal depth	151 mm
Height of installed product	452 mm
Width of installed product	418 mm
Width in division units	18
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Polystyrol (PS)

Type of surface treatment	untreated
Installation, mounting	
Suitable for outdoor use	No
Connection	
Number of conduit inlets	15
Equipment	
Number of rows	2
Quantity of section in width	1
Number of keys	1
Quantity of rails	2
Can be accessorized	Yes
Number of openings for flange plates	46
Extension possible	No
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes
Standards	
GWT Glow wire test	750 °C
European directive WEEE	concerned
Safety	
IK protection code against mechanical impacts	08
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-25...40 °C