



VE218PN

Enclosure,vector,surface mounted,IP65,36M,UV stable, with metric cable entry

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	36
-------------------	----

Compatibility

Suitable for Multimedia	No
-------------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Voltage

Rated operational voltage in DC	1000 V DC
---------------------------------	-----------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	151 mm
Internal depth	151 mm
Height of installed product	452 mm
Width of installed product	418 mm
Width in division units	18
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Connection

Number of conduit inlets	15
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	2
Quantity of section in width	1
Quantity of rails	2
Can be accessorized	Yes
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes

Safety

Protection class	isol.class II
Glow wire test	according EN 60695-2-11: 850°C
REACH conform	No
RoHS conform	Yes

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------