



VF318TJ

**Small distributor,golf,flush,3row,IP40,54M,MS-terminal,N+PE,transparent door**

**Technical properties**

**Functions**

With a pipe-in lead	Yes
---------------------	-----

**Configuration**

Number of modules	54
-------------------	----

**Main electrical features**

Nominal voltage	400 V
-----------------	-------

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Insertion depth	72 mm
Depth of wall niche	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	543 mm
Installation height	507 mm
Width of installed product	460 mm
Width in division units	18
Built-in height	507 mm
Built-in width	426 mm

**Cover, door**

Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

Number of rows	3
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	3
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	0
--------------------------------------	---

Extension possible	Yes
--------------------	-----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	Yes
---------------------	-----

**Standards**

GWT Glow wire test	650 °C
--------------------	--------

**Safety**

IK protection code against mechanical impacts	07
---	----

Protection class	isol.class II
------------------	---------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------