




TYA661A



Dimmer 1 channel 300W

Technical properties

Architecture

Fixing mode Din-Rail

Functions

Bus module detachable No

Multi-phase mode suitable to switch different external conductors

Soft startup bulb-preserving soft startup

Configuration

Number of modules 4

Controls and indicators

With LED indication Yes

Indicator lamp yes

Operation manual operation also possible without bus, e.g. on building site

Manual selection switches / push-buttons selection switch for manual/bus operation as well as load setting

Main electrical features

Frequency 50/60 Hz

Rated current 2.3 A

Voltage

Input voltage 230 V AC

Operating voltage over bus 21...32 V DC

Electric current

Bus current consumption (data transfer) 2.3 mA

Fuse

Fuse overheating protection (display using LEDs)

Dimensions

Width of rail mounted device (RMD) 4 modules

Power

Incandescent bulb power 300 W

Total power loss under IN 4 W

Fluorescent bulbs control

Power lighting fluo lamps 60W

LED control

Max number of LED/CFL lamps	8
Power LED	60 W

Connection

Type of load	universal
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Settings

Supported configuration modes	system
-------------------------------	--------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Type of dimmer	universal
Modular expandability	No
Dimming principle	phase cut-on or cut-off according to load type, self-learning
low noise	very low noise

Use

Local operation/hand operation	Yes
--------------------------------	-----

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

Identification

Main design line	KNX
------------------	-----