



VU12NE

Encl.,Volta,flush,1x12MOD,IP30,Version NCEE

Technical properties

Architecture

Fixing mode flush-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 12

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 63 A

Dimensions

Insertion depth 89 mm

Depth of installed product 98 mm

Internal depth 91.5 mm

Height of installed product 356 mm

Installation height 321 mm

Length 356 mm

Width of installed product 348 mm

Width in division units 12

Thickness of sidewall material 2.5 mm

Built-in height 340 mm

Built-in width 314.5 mm

Cover, door

Type of door closing Latch

Identification of protection index 30

Interlockable No

Number of keylock of the door 0

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated
Installation, mounting	
Suitable for outdoor use	No
Settings	
Enclosure type	Distributor empty cabinet
Scope of delivery	
With cover	No
Equipment	
Number of units	12
Number of rows	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	No
Standards	
GWT Glow wire test	650 °C
European directive WEEE	concerned
Protection class according to IEC-61140	II
Safety	
IK protection code against mechanical impacts	IK07
Protection index IP	IP30
Protection class	isol.class II
Impact strength	IK05
Use conditions	
Operating temperature	-40...40 °C