



TYAS608D



Output module 8-fold 16a c-load adapted

Technical properties

Architecture

Bus system yes

Functions

Multi-phase mode suitable to switch different external conductors

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

Operating mode any combined operation from drive and switching functions possible

Configuration

Number of modules 6

Controls and indicators

Indicator lamp yes

Operation Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; manual operation per channel using button (single-area operation)

Indication / display status LED integrated in the manual operation button

Manual selection switches / push-buttons manual operation buttons for on/off (up/down) and bus function on/off per channel/device

Button / push-button with illuminated programming button

Main electrical features

Rated operational voltage Ue 195 / 253 V

Rated current 16 A

Voltage

Operating voltage over bus 21...32 V DC

Output voltage 230 V~

System supply voltage 30V DC via bus

Electric current

Number of entry circuits 0

Rated current 16 A

Dimensions

Height 90 mm

Power

Output power 2300 W

Max. switching power 2300 W

Lighting control

- uncompensated 1200 VA

LED control

LED Status LED integrated in manual operation button

Incandescent bulbs control

230 V incandescent lamps 2300 W

230 V halogen lamps 2300 W

Connection

Type of load C-Load

Conductor cross-section (flexible) 0.75...2.5 mm²

Bus coupling unit with integral bus coupling unit

Type of connection with QuickConnect plug-in terminals

Bus connection bus connection via connecting terminal

Type of connection quick connect

Settings

Supported configuration modes system

Setting switching time on change of direction adjustable

Scope of delivery

Bus connection included Yes

Equipment

Modular expandability No

Potential-free with potential-free NO contacts as well as NC contact parameterisable

Use

Differentiation characteristic 3 - Sales with plug-in terminals

Safety

REACH conform No

RoHS conform Yes

Halogen free No

Identification

Main design line KNX