



VU12NE

**Encl.,Volta,flush,1x12MOD,IP30,Version NCEE**

### Technical properties

#### Functions

With a pipe-in lead	Yes
---------------------	-----

#### Configuration

Number of modules	12
-------------------	----

#### Main electrical features

Nominal voltage	400 V
-----------------	-------

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Insertion depth	89 mm
Depth of installed product	98 mm
Internal depth	91.5 mm
Height of installed product	356 mm
Installation height	321 mm
Length	356 mm
Width of installed product	348 mm
Width in division units	12
Thickness of sidewall material	2.5 mm
Built-in height	340 mm
Built-in width	314.5 mm

#### Cover, door

Identification of protection index	30
Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

#### Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Subject to technical modifications

Type of surface treatment	untreated
---------------------------	-----------

### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

### Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

### Scope of delivery

With cover	No
------------	----

### Equipment

Number of units	12
-----------------	----

Number of rows	1
----------------	---

Quantity of rails	1
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	0
--------------------------------------	---

Extension possible	Yes
--------------------	-----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	No
------------------------	----

Signal passing door	No
---------------------	----

### Standards

GWT Glow wire test	650 °C
--------------------	--------

Protection class according to IEC-61140	II
-----------------------------------------	----

### Safety

IK protection code against mechanical impacts	IK07
-----------------------------------------------	------

Protection class	isol.class II
------------------	---------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK05
-----------------	------

### Use conditions

Operating temperature	-40...40 °C
-----------------------	-------------