



TYBS692F

**Output module 2x 6A /230V~, 2 inputs, flush mounted, KNX**

**Technical properties**

**Architecture**

Bus system yes

**Functions**

Multi-phase mode for 1 phase operation

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function ; binary input functions: Switching, dimming, blind, value transmitter, scene, priority, timer operation, subplate

**Configuration**

Number of modules 0

**Controls and indicators**

Indicator lamp yes

Operation manual operation in test mode via programming button (single-area operation) ; test mode/building site mode can be activated via programming button

Control for activation of a drive for alternating current

Button / push-button with illuminated programming button

**Connectivity**

Binary inputs with 2 independent binary inputs for potential-free contacts

**Main electrical features**

Rated operational voltage Ue 230 V

Rated current 6 A

**Voltage**

Max. switching capacity at 230 V AC

Operating voltage over bus 21...32 V DC

Output voltage 230 V AC

System supply voltage 30V DC via bus

**Electric current**

Bus current consumption (data transfer) 7 mA

Bus current consumption (idle) 5 mA

Number of entry circuits 2

Maximum through current 6 A

Rated current 6 A

Switching current at  $\cos \varphi = 0.8$  max. 6 A

Withstand current in AC1 for the contact path or zone 1

6 A

### Dimensions

Height of installed product	44 mm
Dimensions (LLxwwxhh)	44 x 43 x 22 mm
Width of rail mounted device (RMD)	0 modules
Height	44 mm

### Power

Max. power with electronic transfo.	500 W
Total power loss under IN	0.5 W
Output power	500 W
Max. switching power	1200 W
Conventional transformers	500 VA
Electronic transformers	500 W

### Measurement

Input scanning voltage	12 V DC V DC
------------------------	--------------

### Lighting control

Fluorescent lamps with electrical ballast (EB)	6 x 48 W
- uncompensated	500 VA

### Fluorescent bulbs control

Power lighting fluo lamps	5 x 13W
Max. power fluo. duo lamp comp. series	6 x 48W

### LED control

Max number of LED/CFL lamps	5
230V LED lamps	5 x 13 W
Power LED	65 W

### Incandescent bulbs control

Max. power with incandescent lamps	500 W
230 V incandescent lamps and halogen lamps	500 W

### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Number of contacts	2
Type of contacts	1NO
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals
Bus connection	bus connection via pre-assembled cable with bus connection terminal
Type of connection	with screw

**Settings**

---

Supported configuration modes	system
-------------------------------	--------

---

Setting	switching time on change of direction adjustable
---------	--

**Scope of delivery**

---

Bus connection included	Yes
-------------------------	-----

**Equipment**

---

Modular expandability	No
-----------------------	----

**Use**

---

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

**Safety**

---

Halogen free	No
--------------	----

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

**Identification**

---

Device family	TYB
---------------	-----

---

Main design line	KNX
------------------	-----