



VU24NE

**Encl.,Volta,flush,2x12MOD,IP30,Version NCEE**

**Technical properties**

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 24

**Main electrical features**

Nominal voltage 400 V

**Electric current**

Rated current 63 A

**Dimensions**

Insertion depth 89 mm

Depth of installed product 98 mm

Internal depth 91.5 mm

Height of installed product 505.5 mm

Installation height 470 mm

Length 505.5 mm

Width of installed product 348 mm

Width in division units 12

Thickness of sidewall material 2.5 mm

Built-in height 490 mm

Built-in width 314.5 mm

**Cover, door**

Identification of protection index 30

Interlockable No

Number of keylock of the door 0

Cover type With Notch

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour pure white

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment

untreated

---

### Installation, mounting

Suitable for outdoor use No

---

### Settings

Enclosure type Distributor empty cabinet

---

### Scope of delivery

With cover No

---

### Equipment

Number of units 12

Number of rows 2

Quantity of rails 2

Can be accessorized Yes

Number of openings for flange plates 0

Extension possible Yes

Earthing terminal block Yes

Neutral terminal block No

Signal passing door No

---

### Standards

GWT Glow wire test 650 °C

Protection class according to IEC-61140 II

---

### Safety

IK protection code against mechanical impacts IK07

Protection class isol.class II

REACH conform No

Halogen free No

Impact strength IK05

---

### Use conditions

Operating temperature -40...40 °C