



WE022G



Push button 1NC+1NO with claws Essensya Pure

Technical properties

Architecture

| | |
|----------------------|-------------|
| Type of control unit | Push button |
| Number of keys | 1 |

Controls and indicators

| | |
|----------------|----|
| Indicator lamp | no |
|----------------|----|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|-------|
| Rated current | 10 AX |
|---------------|-------|

Dimensions

| | |
|---|-------|
| Installation depth, flush-mounted boxes | 40 mm |
| Depth of installed product | 24 mm |
| Height of installed product | 75 mm |
| Width of installed product | 70 mm |

Materials

| | |
|---------------------------|---------------|
| Colour | white |
| Material | polycarbonate |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|---------------|----------------------|
| Fixing type | With screws or claws |
| Mounting type | flush-mounted |

Connection

| | |
|--------------------|---------------|
| Type of contacts | 1NC+1NO |
| Type of connection | quick connect |

Standards

| | |
|-----------|------------|
| Approvals | EN 60669-1 |
|-----------|------------|

Safety

| | |
|---------------|-----|
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

Identification

| | |
|-------------|-----------------------------|
| Range | essensya |
| Composition | Mechanism with upper casing |
