



WNA001B

**cubyko 2-way switch composable white IP55**

**Technical properties**

**Architecture**

|                      |               |
|----------------------|---------------|
| Type of order        | Switch        |
| Type of control unit | single rocker |
| Fixing mode          | Clipped       |

**Controls and indicators**

|                |    |
|----------------|----|
| Indicator lamp | no |
|----------------|----|

**Main electrical features**

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Frequency       | 50/60 Hz |

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 10 AX |
|---------------|-------|

**Dimensions**

|                             |       |
|-----------------------------|-------|
| Depth of installed product  | 40 mm |
| Height of installed product | 75 mm |
| Width of installed product  | 75 mm |

**Capacity**

|                          |   |
|--------------------------|---|
| Number of modules for WA | 2 |
|--------------------------|---|

**Materials**

|            |                       |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
| Material   | polypropylène         |

**Installation, mounting**

|               |                                 |
|---------------|---------------------------------|
| Mounting type | flush mounted / surface mounted |
|---------------|---------------------------------|

**Connection**

|                                    |   |
|------------------------------------|---|
| Connection cross-sect. rigid cable | mini 2x1 mm <sup>2</sup> - maxi 2x2,5 mm <sup>2</sup> |
| Type of contacts                   | 2 way   |
| Type of connection                 | Quickconnect  |

**Standards**

|           |            |
|-----------|------------|
| Approvals | EN 60669-1 |
|-----------|------------|

**Safety**

|   |    |
|---|----|
| IK protection code against mechanical impacts | 07 |
|---|----|

**Identification**

Range

W.1

Composition

Mechanism with upper casing