



TYFS120



KNX/IP Secure interface, 1 module

Technical properties

Architecture

Bus system KNX

Configuration

Number of modules 2

Controls and indicators

Button / push-button with programming button and red programming LED

Connectivity

IP KNXnet/IP Secure according KNX specification : Core, Tunneling, Device Management. Supported internet protocols : ARP, ICMP, IGMP, UDP/IP, TCP/IP, DHCP et Auto IP

Interface as interface to PCs and data processing devices

Voltage

Operating voltage over bus 21...32 V DC

Electric current

Bus consumption 20 mA

Bus current consumption (data transfer) ≈ 20 mA

Dimensions

Assembling height as from DIN rail 65 mm

Width of rail mounted device (RMD) 1 modules

Power

Total power loss under IN 0.6 W

Materials

RAL colour RAL 7035 - Light grey

LED control

LED with green, yellow and red LEDs for communication and status display

Connection

Connection type TG008 (bus and supply voltage) / RJ45 (Ethernet)

Bus coupling unit with integral bus coupling unit

Type of connection operating voltage connection via connecting terminal ; with RJ45 connection for Ethernet/IP networks

Bus connection bus connection via connecting terminal

Settings

Supported configuration modes system

Use conditions

Operating temperature -5...45 °C

Storage/transport temperature -25...70 °C

Identification

Main design line KNX

Instructions

Information text Knowledge of the relevant network technology is required for installation.