



WXF055

Hotel card switch gallery

Technical properties

Architecture

Type of control unit	Hotel card
----------------------	------------

Configuration

Switch mode	2pole
-------------	-------

Controls and indicators

Indicator lamp	no
Push-buttons	Yes

Main electrical features

Nominal voltage	250 V
Frequency	50/60 Hz

Electric current

Rated current	10 A
Switching current	10 A

Dimensions

Insertion depth	75 mm
Depth of installed product	51 mm

Connection

Connection cross-sect. flexible conductor	2,5mm ²
Connection cross-sect. rigid cable	2x2,5mm ²
Type of connection	Quickconnect

Equipment

Lighting	for illumination
----------	------------------

Standards

Approvals	EN 60669-1
-----------	------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...50 °C
Storage/transport temperature	-25...70 °C

Identification	
Range	gallery
Appliance switch type	No