



WXF062

Rotary dimmer Gallery eco lamps

Technical properties

Architecture

Type of control unit	Push & rotative
----------------------	-----------------

Main electrical features

Nominal voltage	230 V
Nominal voltage	230 V
Frequency	50 Hz

Voltage

Operating voltage	230 V AC
-------------------	----------

Dimensions

Height of installed product	45 mm
Dimensions (LLxwxh)	71x71x35

Power

Halogen switching capacity 230V	20 / 300 W
Max. power with electronic transfo.	250 VA
Max. power with electromagnetic transformers	250 VA
Incandescent bulb power	20 / 300 W

Materials

Material	thermoplastic
----------	---------------

LED control

Power LED	50 W
-----------	------

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Connection

Connection cross-sect. flexible conductor	1,5mm ²
Connection cross-sect. rigid cable	1,5 / 2,5mm ²
Type of load	universal
Conductor cross-section	1.5...2.5 mm ²
Type of connection	with screw

Equipment

Dimming principle	phase cut-on or cut-off according to load type, self-learning
-------------------	---

Safety

IK protection code against mechanical impacts	03
REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Storage/transport temperature	-20...60 °C
-------------------------------	-------------

Identification

Range	gallery
-------	---------