



WXF062

**Rotary dimmer Gallery eco lamps**

**Technical properties**

**Architecture**

Type of control unit	Push & rotative
----------------------	-----------------

**Main electrical features**

Nominal voltage	230 V
Nominal voltage	230 V
Frequency	50 Hz

**Voltage**

Operating voltage	230 V AC
-------------------	----------

**Dimensions**

Height of installed product	45 mm
Dimensions (LLxwxh)	71x71x35

**Power**

Halogen switching capacity 230V	20 / 300 W
Max. power with electronic transfo.	250 VA
Max. power with electromagnetic transformers	250 VA
Incandescent bulb power	20 / 300 W

**Materials**

Material	thermoplastic
----------	---------------

**LED control**

Power LED	50 W
-----------	------

**Installation, mounting**

Mounting type	flush-mounted
---------------	---------------

**Connection**

Connection cross-sect. flexible conductor	1,5mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 2,5mm <sup>2</sup>
Type of load	universal
Conductor cross-section	1.5...2.5 mm <sup>2</sup>
Type of connection	with screw

**Equipment**

Dimming principle	phase cut-on or cut-off according to load type, self-learning
-------------------	---

**Safety**

---

IK protection code against mechanical impacts	03
REACH conform	No
RoHS conform	Yes
Halogen free	No

**Use conditions**

---

Storage/transport temperature	-20...60 °C
-------------------------------	-------------

**Identification**

---

Range	gallery
-------	---------