



TYMS616D



**Output module 16-fold 16a c-load adapted**

**Technical properties**

**Architecture**

Bus system yes

**Functions**

Multi-phase mode suitable to switch different external conductors

Function with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function

Switching for switching, e.g. of 16 independent loads or activation of 8 drives

Operating mode any combined operation from drive and switching functions possible

**Configuration**

Number of modules 8

**Controls and indicators**

Indicator lamp yes

Operation Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; manual operation per channel using button (single-area operation)

Indication / display status LED integrated in the manual operation button

Manual selection switches / push-buttons manual operation buttons for on/off (up/down) and bus function on/off per channel/device

Button / push-button with illuminated programming button

**Main electrical features**

Rated operational voltage Ue 230 V

Rated current 16 A

**Voltage**

Operating voltage over bus 21...32 V DC

Output voltage 230 V~

System supply voltage 30V DC via bus

**Electric current**

Bus current consumption (data transfer) 5 mA

Bus current consumption (idle) 3 mA

Number of entry circuits 0

Rated current 16 A

**Dimensions**

Depth	65 mm
Width of rail mounted device (RMD)	8 modules
Height	90 mm
<b>Power</b>	
Max. power with electronic transfo.	1500 W
Total power loss under IN	1.3 W
Output power	2300 W
Max. switching power	25300 W
Conventional transformers	max. 1500 VA
Electronic transformers	1500 W
<b>Lighting control</b>	
Fluorescent lamps with electronical ballast (EB)	max. 20 x 36 W
- uncompensated	1200 VA
<b>Fluorescent bulbs control</b>	
Energy-saving lamps	25 x 18 W
Power lighting fluo lamps	25x18W
Max. power fluo. duo lamp comp. series	27 X 36W
Fluorescent lamps parallel compensated	1000 W /130 µF
<b>LED control</b>	
Max number of LED/CFL lamps	25
230V LED lamps	25 x 18 W
Power LED	450 W
LED	Status LED integrated in manual operation button
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	2300 W
230 V incandescent lamps	2300 W
230 V halogen lamps	2300 W
230 V incandescent lamps and halogen lamps	2300 W
<b>Connection</b>	
Connection cross-sect. flexible conductor	0,5 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	0,5 / 6mm <sup>2</sup>
Type of load	C-Load
Conductor cross-section (flexible)	max. 0.5...4 mm <sup>2</sup>
Conductor cross-section (rigid)	max. 0.5...6 mm <sup>2</sup>
Type of contacts	16F
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
Type of connection	quick connect
<b>Settings</b>	
Supported configuration modes	system

Subject to technical modifications

**Scope of delivery**

---

Bus connection included	Yes
-------------------------	-----

**Equipment**

---

Modular expandability	No
-----------------------	----

---

Potential-free	with potential-free NO contacts as well as NC contact parameterisable
----------------	--

**Use**

---

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

**Safety**

---

REACH conform	No
---------------	----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	No
--------------	----

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

**Identification**

---

Device family	TYM
---------------	-----

---

Main design line	KNX
------------------	-----