



UC463XRN

MCCB horizontal kit, quadro evo, H3+ x630, 598x298 mm with RCB

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 188 mm |
| Height of installed product | 300 mm |
| Width of installed product | 600 mm |

Capacity

| | |
|--|---|
| Quantity of half modules terminales per rail | 0 |
|--|---|

Cover, door

| | |
|------------|-------|
| Cover type | Cover |
|------------|-------|

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 9010 - Pure white |
|------------|-----------------------|

Installation, mounting

| | |
|--|---|
| Quantity of terminal steps in 1/2 modules on kit | 0 |
|--|---|

Scope of delivery

| | |
|------------|-----|
| With cover | Yes |
|------------|-----|

Equipment

| | |
|------------------------------|-----|
| Number of units | 1 |
| Number of rows | 0 |
| Quantity of section in width | 2 |
| Quantity of rails | 0 |
| Can be accessorized | Yes |
| Quantity of steps in height | 6 |

Standards

| | |
|-----------|---------------|
| Approvals | EN 61439-1/-2 |
|-----------|---------------|

Safety

| | |
|------------------|--------------|
| Protection class | isol.class I |
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | Yes |