



WXF421E

Socket for trunking gallery 2P+E 16A orange

Technical properties

Architecture

| | |
|--------------|------|
| Type of pole | 2P+T |
|--------------|------|

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 250 V |
|-----------------|-------|

Electric current

| | |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

Dimensions

| | |
|-------|-------|
| Depth | 45 mm |
|-------|-------|

| | |
|--------|---------|
| Height | 43.5 mm |
|--------|---------|

| | |
|-------|---------|
| Width | 67.5 mm |
|-------|---------|

Cover, door

| | |
|-------|------------------|
| Cover | Complete housing |
|-------|------------------|

Materials

| | |
|--------|--------|
| Colour | orange |
|--------|--------|

| | |
|---------------------------|-----------|
| Type of surface treatment | untreated |
|---------------------------|-----------|

Connection

| | |
|--------------------|--------------|
| Type of connection | Quickconnect |
|--------------------|--------------|

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-----------|-----------|
| Approvals | NFC 61314 |
|-----------|-----------|

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---|----|
| IK protection code against mechanical impacts | 07 |
|---|----|

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

| | |
|------------|-----------------------------|
| Protection | Enhanced contact protection |
|------------|-----------------------------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10...35 °C |
|-----------------------|-------------|

Storage/transport temperature

-10...50 °C

Identification

Composition

Mechanism with upper casing