



WXF436T

Switch 16AX multi sockets Gallery 2P+E titane

Technical properties

Architecture

| | |
|----------------------|---------------|
| Type of order | Switch |
| Type of pole | 2P+T |
| Type of control unit | single rocker |
| Fixing mode | Clipped |

Configuration

| | |
|-------------------------|----|
| Antibacterial treatment | No |
|-------------------------|----|

Compatibility

| | |
|-------------------------|----|
| IFTTT support available | No |
|-------------------------|----|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|---------------|-------|
| Rated current | 16 AX |
|---------------|-------|

Dimensions

| | |
|-----------------|-------|
| Depth | 52 mm |
| Insertion depth | 52 mm |
| Height | 45 mm |
| Width | 45 mm |

Materials

| | |
|------------------------------|--------------|
| Free area for finishing name | titane |
| Surface appearance | satın finish |
| Type of surface treatment | untreated |

Connection

| | |
|---|--------------------------|
| Connection cross-sect. flexible conductor | 0,5 / 2,5mm ² |
| Connection cross-sect. rigid cable | 0,5 / 2,5mm ² |
| Type of connection | Quickconnect |

Equipment

| | |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

Standards

| | |
|-----------|------------|
| Approvals | EN 60669-1 |
|-----------|------------|

| | | |
|---|--|-----------------------------|
| Safety | | |
| IK protection code against mechanical impacts | | 05 |
| Use conditions | | |
| Operating temperature | | -10...35 °C |
| Storage/transport temperature | | -10...50 °C |
| Identification | | |
| Range | | gallery |
| Composition | | Mechanism with upper casing |