



VD212TF

**Small distributor, IC<sup>2</sup>, surface, 2 row, 24M, IP40, MS-terminal, N, transparent door**

**Technical properties**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Functions**

With a pipe-in lead	Yes
---------------------	-----

**Configuration**

Number of modules	24
-------------------	----

**Main electrical features**

Nominal voltage	400 V
-----------------	-------

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth of installed product	92.5 mm
Internal depth	72 mm
Height of installed product	326.5 mm
Width of installed product	294 mm
Width in division units	24

**Cover, door**

Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

**Materials**

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Polystyrol (PS)
Type of surface treatment	untreated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Number of rows	2
Quantity of section in width	1
Number of keys	1
Quantity of rails	2
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	No
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

**Standards**

GWT Glow wire test	650 °C
European directive WEEE	not concerned

**Safety**

IK protection code against mechanical impacts	IK07
Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------