



VE103PN

Enclosure, vector, flush mounted, IP65, 3M, UV stable, with metric cable entry

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	3
-------------------	---

Main electrical features

Nominal voltage	400 V
-----------------	-------

Voltage

Rated operational voltage in DC	1000 V DC
---------------------------------	-----------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	93 mm
Internal depth	93 mm
Height of installed product	175 mm
Width of installed product	111 mm
Width in division units	3
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

Materials

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Polycarbonate (PC)

Subject to technical modifications

Type of surface treatment	untreated
Installation, mounting	
Suitable for outdoor use	Yes
Connection	
Number of conduit inlets	2
Equipment	
Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Extension possible	No
Signal passing door	Yes
Standards	
GWT Glow wire test	850 °C
European directive WEEE	concerned
Safety	
IK protection code against mechanical impacts	IK07
Protection class	isol.class II
Glow wire test	according EN 60695-2-11: 850°C
REACH conform	No
RoHS conform	Yes
Use conditions	
Operating temperature	-25...40 °C