



WXP0196

**Plate gallery plastic plastic1K 8 modules + 8 modules titane**

**Technical properties**

**Architecture**

|             |         |
|-------------|---------|
| Fixing mode | Clipped |
|-------------|---------|

**Configuration**

|                   |    |
|-------------------|----|
| Number of modules | 16 |
|-------------------|----|

**Dimensions**

|        |        |
|--------|--------|
| Depth  | 9.3 mm |
| Height | 164 mm |
| Width  | 235 mm |

**Capacity**

|                   |   |
|-------------------|---|
| Number of sockets | 2 |
|-------------------|---|

**Materials**

|                              |                            |
|------------------------------|----------------------------|
| Free area for finishing name | titane                     |
| Colour                       | aluminium optics           |
| RAL colour                   | RAL 9006 - White aluminium |
| Surface appearance           | matt                       |
| Type of surface treatment    | Painted                    |

**Installation, mounting**

|              |            |
|--------------|------------|
| Mounting way | horizontal |
|--------------|------------|

**Equipment**

|                                       |    |
|---------------------------------------|----|
| With transparent product label holder | No |
|---------------------------------------|----|

**Standards**

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

|   |    |
|---|----|
| IK protection code against mechanical impacts | 05 |
|---|----|

**Use conditions**

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -10...35 °C |
| Storage/transport temperature | -10...50 °C |

**Identification**

|             |                       |
|-------------|-----------------------|
| Range       | gallery               |
| Composition | Surface mounted frame |