



XEV102

**EV charging station witty home 1x7kW 1P M3T2S M2TE IP54**

**Technical properties**

**Architecture**

Connection system	Typ 2
Fixing mode	Wall mounting

**Functions**

Function access control	No
With load management	Yes

**Connectivity**

Number of charging points	1
Number of CEE socket outlets	0
Number of socket outlets GB	0
Number of socket outlets Type 2	1
Number of socket outlets Type 3	0
Number of vehicle connectors CHAdeMO	0
Number of vehicle connectors Type 1	0
Number of vehicle connectors Type 1 CCS	0
Number of vehicle connectors Type 2	0
Number of vehicle connectors Type 2 CCS	0

**Main electrical features**

Nominal voltage	230 V
Frequency	50 Hz
Rated current	32 A

**Dimensions**

Depth of installed product	233 mm
Height of installed product	480 mm
Length	480 mm
Width of installed product	346 mm

**Power**

connected load	8 kW
Max. power per charging point	7.4 kW

**Power supply**

Number of phases for the power supply	1 phase
---------------------------------------	---------

**Materials**

Colour	light grey
--------	------------

RAL colour	RAL 7035 - Light grey
Material	plastic
Material group	other
<b>Scope of delivery</b>	
Number of earth leakage circuit breakers type A	1
<b>Equipment</b>	
With energy meter	Yes
With house connection box	No
Number of household socket outlets	1
Number of vehicle connectors GB AC	0
Number of vehicle connectors GB DC	0
With circuit breaker	Yes
<b>Standards</b>	
European directive RoHS	compliant
<b>Safety</b>	
Protection index IP	IP54
Impact strength	IK10