



VE103SN

Enclosure,vector,flush mounted,IP65,3M,UV stable,without cable entry

Technical properties

Architecture

Fixing mode surface-mounting

Functions

With a pipe-in lead Yes

Configuration

Number of modules 3

Main electrical features

Nominal voltage 400 V

Voltage

Rated operational voltage in DC 1000 V DC

Electric current

Rated current 63 A

Dimensions

Depth of installed product 93 mm

Internal depth 93 mm

Height of installed product 175 mm

Width of installed product 111 mm

Width in division units 3

Thickness of sidewall material 2.5 mm

Cover, door

Type of door closing Latch

Identification od protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment

untreated

Installation, mounting

Suitable for outdoor use

Yes

Connection

Number of conduit inlets

2

Settings

Enclosure type

Distributor empty cabinet

Equipment

Number of rows

1

Quantity of section in width

1

Quantity of rails

1

Can be accessorized

Yes

Extension possible

No

Signal passing door

Yes

Standards

GWT Glow wire test

850 °C

European directive WEEE

concerned

Safety

Protection class

isol.class II

Glow wire test

according EN 60695-2-11: 850°C

Use conditions

Operating temperature

-25...40 °C