



VE103SN

**Enclosure, vector, flush mounted, IP65, 3M, UV stable, without cable entry**

**Technical properties**

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 3

**Main electrical features**

Nominal voltage 400 V

**Voltage**

Rated operational voltage in DC 1000 V DC

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 93 mm

Internal depth 93 mm

Height of installed product 175 mm

Width of installed product 111 mm

Width in division units 3

Thickness of sidewall material 2.5 mm

**Cover, door**

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Material Polycarbonate (PC)

Type of surface treatment untreated

**Installation, mounting**

Suitable for outdoor use Yes

Subject to technical modifications

---

**Connection**

Number of conduit inlets	2
--------------------------	---

---

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

---

**Equipment**

Number of rows	1
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	1
-------------------	---

Can be accessorized	Yes
---------------------	-----

Extension possible	No
--------------------	----

Signal passing door	Yes
---------------------	-----

---

**Standards**

GWT Glow wire test	850 °C
--------------------	--------

European directive WEEE	concerned
-------------------------	-----------

---

**Safety**

IK protection code against mechanical impacts	IK07
---	------

Glow wire test	according EN 60695-2-11: 850°C
----------------	--------------------------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

---

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------