



XEV201C

EV charging station witty park 1x7kW 1P M3T2S M2TE IP54 ÏP

Technical properties

Architecture

| | |
|-------------------|-------|
| Connection system | Typ 2 |
|-------------------|-------|

Functions

| | |
|-------------------------|-----|
| Function access control | Yes |
| With load management | Yes |

Connectivity

| | |
|---|---|
| Number of charging points | 1 |
| Number of CEE socket outlets | 0 |
| Number of socket outlets GB | 0 |
| Number of socket outlets Type 2 | 1 |
| Number of socket outlets Type 3 | 0 |
| Number of vehicle connectors CHAdeMO | 0 |
| Number of vehicle connectors Type 1 | 0 |
| Number of vehicle connectors Type 1 CCS | 0 |
| Number of vehicle connectors Type 2 | 0 |
| Number of vehicle connectors Type 2 CCS | 0 |

Main electrical features

| | |
|-----------------|-------|
| Nominal voltage | 230 V |
| Frequency | 50 Hz |
| Rated current | 32 A |

Dimensions

| | |
|-----------------------------|--------|
| Depth of installed product | 233 mm |
| Height of installed product | 480 mm |
| Length | 480 mm |
| Width of installed product | 346 mm |

Power

| | |
|-------------------------------|--------|
| connected load | 8 kW |
| Max. power per charging point | 7.4 kW |

Power supply

| | |
|---------------------------------------|---------|
| Number of phases for the power supply | 1 phase |
|---------------------------------------|---------|

Materials

| | |
|------------|-----------------------|
| RAL colour | RAL 7035 - Light grey |
| Material | plastic |

Material group other

Scope of delivery

Number of earth leakage circuit breakers
type A 1

Equipment

With energy meter Yes

With house connection box No

Number of household socket outlets 1

Number of vehicle connectors GB AC 0

Number of vehicle connectors GB DC 0

With circuit breaker Yes

Standards

European directive RoHs compliant

Safety

Protection index IP IP54

REACH conform No

Impact strength IK10