



VE105A

Enclosure,vector,6M, red, with glass sheet

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	6
-------------------	---

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth of installed product	113 mm
Internal depth	113 mm
Height of installed product	190 mm
Width of installed product	165 mm
Width in division units	6
Thickness of sidewall material	2.5 mm

Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	with key
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Type of surface treatment	untreated
---------------------------	-----------

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Connection

Number of conduit inlets	3
--------------------------	---

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
Quantity of section in width	1
Number of keys	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	6
Extension possible	No

Standards

GWT Glow wire test	750 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
Impact strength	IK07

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------