



XEV601C

**EV charging station witty park 2x22kW 3P M3T2S M2TE IP54 IP**

**Technical properties**

**Architecture**

Connection system	Typ 2
-------------------	-------

**Functions**

Function access control	Yes
With load management	No

**Connectivity**

Number of charging points	2
Number of CEE socket outlets	0
Number of socket outlets GB	0
Number of socket outlets Type 2	2
Number of socket outlets Type 3	0
Number of vehicle connectors CHAdeMO	0
Number of vehicle connectors Type 1	0
Number of vehicle connectors Type 1 CCS	0
Number of vehicle connectors Type 2	0
Number of vehicle connectors Type 2 CCS	0

**Main electrical features**

Nominal voltage	230/400 V
Frequency	50/60 Hz
Rated current	32 A

**Dimensions**

Depth of installed product	202 mm
Height of installed product	760 mm
Length	765 mm
Width of installed product	355 mm

**Power**

connected load	44 kW
Max. power per charging point	22 kW

**Power supply**

Number of phases for the power supply	3-phase
---------------------------------------	---------

**Materials**

Material group	stainless steel
----------------	-----------------

**Equipment**

Subject to technical modifications

With energy meter	Yes
With house connection box	No
Number of household socket outlets	2
Number of vehicle connectors GB AC	0
Number of vehicle connectors GB DC	0
With circuit breaker	No

#### Standards

European directive RoHs	compliant
-------------------------	-----------

#### Safety

Protection index IP	IP54
REACH conform	No
Impact strength	IK10