



VE106SN

Enclosure,vector,flush mounted,IP65,6M,UV stable,without cable entry

#### Technical properties

##### Functions

With a pipe-in lead	Yes
---------------------	-----

##### Configuration

Number of modules	6
-------------------	---

##### Main electrical features

Nominal voltage	400 V
-----------------	-------

##### Voltage

Rated operational voltage in DC	1000 V DC
---------------------------------	-----------

##### Electric current

Rated current	63 A
---------------	------

##### Dimensions

Depth of installed product	113 mm
----------------------------	--------

Internal depth	113 mm
----------------	--------

Height of installed product	190 mm
-----------------------------	--------

Width of installed product	165 mm
----------------------------	--------

Width in division units	6
-------------------------	---

Thickness of sidewall material	2.5 mm
--------------------------------	--------

##### Cover, door

Identification of protection index	65
------------------------------------	----

Interlockable	No
---------------	----

Number of keylock of the door	0
-------------------------------	---

Cover type	Closed (plain)
------------	----------------

Door locking	without
--------------	---------

Door leave	single
------------	--------

Cover type	Door
------------	------

Transparent cover or door	Yes
---------------------------	-----

##### Materials

Colour	light grey
--------	------------

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Type of surface treatment	untreated
---------------------------	-----------

##### Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

**Connection**

Number of conduit inlets	3
--------------------------	---

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

Number of rows	1
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	1
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	16
--------------------------------------	----

Extension possible	No
--------------------	----

Earthing terminal block	No
-------------------------	----

Neutral terminal block	No
------------------------	----

Signal passing door	Yes
---------------------	-----

**Standards**

GWT Glow wire test	850 °C
--------------------	--------

**Safety**

IK protection code against mechanical impacts	IK07
-----------------------------------------------	------

Protection class	isol.class II
------------------	---------------

Glow wire test	according EN 60695-2-11: 850°C
----------------	--------------------------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------