



14093515

FCC soc.out. insert 8p shielded hinged cover surf./flushmtd,cat.6,labfield,W1,gr

Technical characteristics

Architecture

Design to according to DIN EN 60603-7-5

Connectivity

Plug type for RJ11, RJ12 and RJ45 plugs

Voltage

Voltage suitable for PoE+

Frequency

Transmission bandwidth 250 MHz

Cover, door

Hinged covers with transparent hinged cover

Materials

Colour code A and B according to TIA/EIA-568-B.2

Material / surface Housing made of die-cast zinc

Connection

Cat.6, Class E according to DIN EN 50173-1:2011-09

Type of connection with cutting terminals

Contact with screen contacting 360° and strain relief

Cat.6/class E according to ISO/IEC 11801. 2nd edition

Use

Differentiation characteristic 1 - Sales with labelling field

Safety

REACH conform Yes

RoHS conform Yes

Protection with self-closing dust protection cover before jack

Use conditions

Operating temperature -40...30 °C

Storage/transport temperature -50...50 °C

Identification

Application, usage Communication technology

Main design line Berker W.1

Instructions

