



VE109A

**Enclosure,vector,10M,red,with glass plate**

**Technical properties**

**Architecture**

Fixing mode	surface-mounting
-------------	------------------

**Functions**

With a pipe-in lead	Yes
---------------------	-----

**Configuration**

Number of modules	10
-------------------	----

**Main electrical features**

Nominal voltage	400 V
-----------------	-------

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth of installed product	114 mm
Internal depth	114 mm
Height of installed product	210 mm
Width of installed product	237 mm
Width in division units	10
Thickness of sidewall material	2.5 mm

**Cover, door**

Type of door closing	Latch
Identification od protection index	55
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	with key
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	red
Type of surface treatment	untreated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	6
--------------------------	---

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

Number of rows	1
----------------	---

Quantity of section in width	1
------------------------------	---

Number of keys	1
----------------	---

Quantity of rails	1
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	6
--------------------------------------	---

Extension possible	No
--------------------	----

**Standards**

GWT Glow wire test	750 °C
--------------------	--------

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP55
---------------------	------

Protection class	isol.class II
------------------	---------------

Impact strength	IK07
-----------------	------

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------