



16402035

Relay switch centre plate for hotel card, 1930/R.classic, black glossy

Technical characteristics

Architecture

Number of keys 0

Configuration

Switch mode 1pole

Antibacterial treatment No

Main electrical features

Nominal voltage 230 V

Rated voltage 230 V AC

Frequency 50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$ max. 6 A

Dimensions

Depth 60 mm

Insertion depth 32 mm

Card width max. 55 mm

Card thickness 0.8...1.2 mm

Power

Conventional transformers 1500 VA

Electronic transformers 1500 W

Power consumption < 0.2 W

Materials

Colour of design line black

Surface appearance glossy

Fluorescent bulbs control

Compact fluorescent lamps 500 W

Fluorescent lamps in duo circuit 1500 W

LED control

LED illuminated with blue LED if hotel card is not inserted

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 1500 W

Installation, mounting

Connection

Screw terminals (max.)	2 x 2,5 mm ²
Type of connection	with screw-in lift terminals

Settings

Delay time incrementally adjustable	0, 15, 30, 60 s
Setting	with potentiometer for incremental adjustment of delay time

Equipment

Lighting	for illumination
Potential-free	with potential-free contact
Centre plates / central plates	with centre plate Ø 58 mm

Use cases

Application	Light control ; Hotel application
-------------	-----------------------------------

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...50 °C
Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)

Identification

Application, usage	Light control
Main design line	Serie 1930/R.classic
Secondary design line(s)	Serie 1930 ; Series R.classic

Instructions

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--