



16402035

Relay switch centre plate for hotel card, 1930/R.classic, black glossy

Technical characteristics

Architecture

Number of keys	0
Fixing mode	flush-mounting

Configuration

Switch mode	1pole
Antibacterial treatment	No

Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$	max. 6 A
----------------------------------------	----------

Dimensions

Depth	60 mm
Insertion depth	32 mm
Card width	max. 55 mm
Card thickness	0.8...1.2 mm

Power

Conventional transformers	1500 VA
Electronic transformers	1500 W

Materials

Colour of design line	black
Colour	black
Colour	deep black
RAL colour	RAL 9005 - Jet black
Material	Plastic/metal

Fluorescent bulbs control

Compact fluorescent lamps	500 W
Fluorescent lamps in duo circuit	1500 W

LED control

LED	illuminated with blue LED if hotel card is not inserted
-----	---------------------------------------------------------

Incandescent bulbs control

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Screw terminals (max.)	2 x 2,5 mm ²
------------------------	-------------------------

Type of connection	with screw-in lift terminals
--------------------	------------------------------

Settings

Delay time incrementally adjustable	0, 15, 30, 60 s
-------------------------------------	-----------------

Setting	with potentiometer for incremental adjustment of delay time
---------	-------------------------------------------------------------

Equipment

Lighting	for illumination
----------	------------------

Potential-free	with potential-free contact
----------------	-----------------------------

Centre plates / central plates	with centre plate Ø 58 mm
--------------------------------	---------------------------

Use cases

Application	Light control, Hotel application
-------------	----------------------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	----------------------------------------------------------

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Serie 1930/R.classic
------------------	----------------------

Secondary design line(s)	Serie 1930, Series R.classic
--------------------------	------------------------------

Instructions

Special note text	Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!
-------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------