



VE110PN

Enclosure, vector, flush mounted, IP65, 10M, UV-stable, with metric cable entry

Technical properties

Functions

With a pipe-in lead Yes

Configuration

Number of modules 10

Compatibility

Suitable for Multimedia No

Main electrical features

Nominal voltage 400 V

Voltage

Rated operational voltage in DC 1000 V DC

Electric current

Rated current 63 A

Dimensions

Depth of installed product 114 mm

Internal depth 114 mm

Height of installed product 210 mm

Width of installed product 237 mm

Width in division units 10

Thickness of sidewall material 2.5 mm

Cover, door

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

Materials

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Connection

Number of conduit inlets	6
--------------------------	---

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
----------------	---

Quantity of section in width	1
------------------------------	---

Quantity of rails	1
-------------------	---

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	20
--------------------------------------	----

Extension possible	No
--------------------	----

Earthing terminal block	No
-------------------------	----

Neutral terminal block	No
------------------------	----

Signal passing door	Yes
---------------------	-----

Standards

GWT Glow wire test	850 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	IK07
---	------

Protection class	isol.class II
------------------	---------------

Glow wire test	according EN 60695-2-11: 850°C
----------------	--------------------------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------