



16406092

Relay switch with centre plate for hotel card, Q.1/Q.3/Q.7, white velvety

Technical characteristics

Architecture

Number of keys	0
Fixing mode	flush-mounting

Configuration

Antibacterial treatment	No
-------------------------	----

Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

Electric current

Inductive load at $\cos \varphi = 0.6$	max. 6 A
--	----------

Dimensions

Depth	57.3 mm
Insertion depth	32 mm
Card width	max. 55 mm
Card thickness	0.8...1.2 mm
Height	71 mm
Width	71 mm

Power

Conventional transformers	1500 VA
Electronic transformers	1500 W

Materials

Colour	white
RAL colour	RAL 1013 - Oyster white
Material	Plastic/metal
Surface appearance	velvety

Fluorescent bulbs control

Compact fluorescent lamps	500 W
Fluorescent lamps in duo circuit	1500 W

LED control

LED	illuminated with blue LED if hotel card is not inserted
-----	---

Incandescent bulbs control

Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

Connection

Screw terminals (max.)	2 x 2,5 mm ²
------------------------	-------------------------

Type of connection	with screw-in lift terminals
--------------------	------------------------------

Settings

Delay time incrementally adjustable	0, 15, 30, 60 s
-------------------------------------	-----------------

Setting	with potentiometer for incremental adjustment of delay time
---------	---

Equipment

Lighting	for illumination
----------	------------------

Potential-free	with potential-free contact
----------------	-----------------------------

Use cases

Application	Light control
-------------	---------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...50 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------

Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
--------------------------	--