



VE112F

**Enclosure,vector, IP55, 12M**

**Technical properties**

**Functions**

With a pipe-in lead Yes

**Configuration**

Number of modules 12

**Compatibility**

Suitable for Multimedia No

**Main electrical features**

Nominal voltage 400 V

**Electric current**

Rated current 63 A

**Dimensions**

Depth of installed product 151 mm

Internal depth 151 mm

Height of installed product 302 mm

Width of installed product 310 mm

Width in division units 12

Thickness of sidewall material 2.5 mm

**Cover, door**

Identification of protection index 65

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment untreated

**Installation, mounting**

Suitable for outdoor use No

**Connection**

Number of conduit inlets	12
--------------------------	----

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

Number of rows	1
Quantity of section in width	1
Number of keys	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	46
Extension possible	No
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes

**Standards**

GWT Glow wire test	750 °C
--------------------	--------

**Safety**

IK protection code against mechanical impacts	IK08
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK08

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------