



VE112SN

**Enclosure,vector,surface mounted,IP65,1x12M,UV stable, without cable entry**

## Technical properties

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Functions

With a pipe-in lead	Yes
---------------------	-----

### Configuration

Number of modules	12
-------------------	----

### Main electrical features

Nominal voltage	400 V
-----------------	-------

### Voltage

Rated operational voltage in DC	1000 V DC
---------------------------------	-----------

### Electric current

Rated current	63 A
---------------	------

### Dimensions

Depth of installed product	151 mm
Internal depth	151 mm
Height of installed product	302 mm
Width of installed product	310 mm
Width in division units	12
Thickness of sidewall material	2.5 mm

### Cover, door

Identification of protection index	65
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	Yes

### Materials

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Polycarbonate (PC)

Subject to technical modifications

Type of surface treatment	untreated
<b>Installation, mounting</b>	
Suitable for outdoor use	Yes
<b>Connection</b>	
Number of conduit inlets	12
<b>Equipment</b>	
Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	46
Extension possible	No
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes
<b>Standards</b>	
GWT Glow wire test	850 °C
European directive WEEE	concerned
<b>Safety</b>	
Protection class	isol.class II
Glow wire test	according EN 60695-2-11: 850°C
REACH conform	No
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	-25...40 °C