



16409909

**Relay switch centre plate for hotel card, S.1/B.3/B.7, p. white, matt, plastic**

**Technical characteristics**

**Architecture**

Number of keys	0
Fixing mode	flush-mounting

**Configuration**

Switch mode	1pole
Antibacterial treatment	No

**Main electrical features**

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

**Electric current**

Inductive load at $\cos \varphi = 0.6$	max. 6 A
Switching current	10 A /230 V AC1

**Dimensions**

Depth	57.3 mm
Insertion depth	32 mm
Card width	max. 55 mm
Card thickness	0.8...1.2 mm
Height	71 mm
Width	71 mm

**Power**

Conventional transformers	1500 VA
Electronic transformers	1500 W

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	Plastic/metal
Surface appearance	matt

**Fluorescent bulbs control**

Compact fluorescent lamps	500 W
Fluorescent lamps in duo circuit	1500 W

**LED control**

LED illuminated with blue LED if hotel card is not inserted

**Incandescent bulbs control**

230 V incandescent lamps and halogen lamps 1500 W

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Screw terminals (max.) 2 x 2,5 mm<sup>2</sup>

Type of connection with screw-in lift terminals

**Settings**

Delay time incrementally adjustable 0, 15, 30, 60 s

Setting with potentiometer for incremental adjustment of delay time

**Equipment**

Lighting for illumination

Potential-free with potential-free contact

**Use cases**

Application Light control, Hotel application

**Safety**

Protection index IP IP20

**Use conditions**

Operating temperature -5...50 °C

Storage/transport temperature -25...70 °C (storage at > 45°C reduces the service life)

**Identification**

Application, usage Light control

Main design line Berker S.1/B.3/B.7

Secondary design line(s) Berker S.1, Berker B.3, Berker B.7