



16417114

## Relay switch centre plate for hotel card, K.5, stainless steel lacq.

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Configuration

Switch mode	1pole
Antibacterial treatment	No

#### Main electrical features

Nominal voltage	230 V
Rated voltage	230 V AC
Frequency	50/60 Hz

#### Electric current

Inductive load at $\cos \varphi = 0.6$	max. 6 A
Switching current	10 A / 230 V AC1

#### Dimensions

Depth	58.6 mm
Insertion depth	32 mm
Card width	max. 55 mm
Card thickness	0.8...1.2 mm
Height	71 mm
Width	71 mm

#### Power

Conventional transformers	1500 VA
Electronic transformers	1500 W

#### Materials

Colour of design line	stainless steel
Colour	stainless steel
Colour	stainless steel optics
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	lacquered
Material	Plastic/metal
Surface appearance	matt

#### Fluorescent bulbs control

Compact fluorescent lamps	500 W
Fluorescent lamps in duo circuit	1500 W

<b>LED control</b>	
LED	illuminated with blue LED if hotel card is not inserted
<b>Incandescent bulbs control</b>	
230 V incandescent lamps and halogen lamps	1500 W
<b>Installation, mounting</b>	
Installation mode	with spreader claws
<b>Connection</b>	
Screw terminals (max.)	2 x 2,5 mm <sup>2</sup>
Type of connection	with screw-in lift terminals
<b>Settings</b>	
Delay time incrementally adjustable	0, 15, 30, 60 s
Setting	with potentiometer for incremental adjustment of delay time
<b>Equipment</b>	
Lighting	for illumination
Potential-free	with potential-free contact
<b>Use cases</b>	
Application	Light control, Hotel application
<b>Safety</b>	
Protection index IP	IP20
REACH conform	No
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-5...50 °C
Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
<b>Identification</b>	
Application, usage	Light control
Main design line	Berker K.5